

# MotionPro HS-4

Plug-N-Play High-Speed Imaging



Redlake's *MotionPro*® HS-4 high-speed motion camera combines excellent resolution to frame rate performance, along with the advanced features you require for accurate high-speed motion analysis on your PC or Mac laptop or desktop computer. The blazing speed of the *MotionPro*® HS-4 of over 5000 fps at 512 x 512 is perfect for research and development labs and airbag testing applications.

With the *MotionPro*® HS-4 camera integration could not be simpler. Just install the software, connect one or more HS Series cameras to USB 2.0 ports or hub, and you are ready to capture high-speed digital imagery. Control the camera system with the feature-rich MotionPro Central software or use the LabVIEW™ or MATLAB® plug-in. To create your own control software, a SDK is included.

## Features

- Up to 512 x 512 resolution color or mono
- Fast frame rates over 5000 fps at full resolution to over 140,000 fps at reduced resolution
- Supports up to 3 seconds record time at full resolution
- LabVIEW™ and MATLAB® plug-ins
- 100 nanosecond inter-frame time in double exposure mode for the capture and analysis of high speed events
- FlexROI™ Configurable Region of Interest for selection of precise field of view to maximize performance

The extensive image processing algorithms include binning (2x2, 3x3, and 4x4), filtering, advanced color control, and programmable LUT enable you to maximize the image quality under various lighting conditions.

Image capture with *MotionPro*® HS-4 camera may be initiated via software or a wide variety of external triggers including optical, acoustic, or electrical, as well as simple hand-held switches. Flexible recording options allow the user to capture pre-selected numbers of frames before and/or after receiving a trigger or to employ a double-exposure mode, which, with a 100 nanoseconds inter-frame time, is perfect for motion analysis on objects moving at very high speeds. Memory may be divided into multiple sessions with or without automatic download to assure no event is missed.



## Applications

- Microscopy
- Automotive Airbag Safety Testing
- Biomechanical Research
- Fluid Dynamics Research (PIV)



officially licensed by



# MotionPro HS-4

## Plug-N-Play High-Speed Imaging

### Performance Specifications

#### CMOS Imager

Sensor Array	Area Array with 16 $\mu$ m x 16 $\mu$ m pixels, color or monochrome
Image Resolution	Up to 512 x 512 at 5000 fps
Dynamic Range	59 dB at sensor

#### Memory and Record Rates

On-Board Storage	4 GB
Recording Rates	Selectable, up to 140,000 fps
Playback Rates	User selectable

#### Camera Control

Shutter	Global Electronic Shutter variable to 1 $\mu$ s, optional 100 nanosecond exposure*
Trigger Frame	Variable position from start to the maximum available frame capacity
Trigger Mode	CMOS level (3.3v) via BNC connectors
Time Stamp	Each frame

#### Software

Control Software	MotionPro Central; Windows 2000, XP, Mac OS X compatible
Image Processing Algorithms	Binning, filtering, advance color control, and programmable LUT
Plug-ins	LabVIEW™ for PC; MATLAB® for PC and Mac; Twain Driver for PC and Mac
File Formats	TIFF, BMP, PNG, MRF, MCF, AVI, BLD, MPEG, and MOV (Mac only)

#### Mechanical Description

Camera Size	Dimensions: 3.7"(H) x 3.7 "(W) x 6.4" (L) 95 x 95 x 162mm); Weight: 4.2 lbs (1.9Kg)
Camera to PC Interface	USB 2.0 Sync I/O; Trigger In; Power
Camera Cable Lengths	Camera to PC: up to 90 ft (30m) with option extension cables
Lens Compatibility	1" C-mount
Lens Mount	C-mount, F-mount adapter (Nikon or Canon)

#### Synchronization

Synchronization (USB Hub Optional)	All cameras are synchronized with each other using an external sync pulse on 3.3v CMOS BNC connector
------------------------------------	--

#### Environmental

Camera Power	+24 vdc (100-240 VAC, 50-60 Hz ac/dc convertor)
Operating Temperature	+5°C to +40°C Ambient (0°F to 122°F)
Emission/Safety	CE approved, FCC Class B compliant, UL listed

\*MotionPro SI-4

Note: Specifications are subject to change without notice

### Sample Frame Rates


Vertical Resolution	Max. Horiz. Resolution = 512
512	>5000
256	>10,000
128	>20,000
64	>35,000
32	>75,000
16	>140,000

Note: Horizontal resolution does not affect frame rate performance. All HS cameras can record at any frame rate at full horizontal resolution.

### Accessories

HS Timing Hub	USB digital interface, integrated control software with 8 outputs, 2 inputs
USB Repeater	For use up to 15m

### Spectral Range



### Camera Back



#### Input/Output

Trig In  
Sync In  
Sync Out  
USB 2.0 Interface  
DC Power

### Worldwide Sales and Support



#### Americas

tel: +1-800-462-4307  
tel: +1-858-481-8182  
sales@redlake.com

#### Asia Pacific

tel: +65-6293-4758  
salesASPAC@redlake.com

#### Europe, Africa, Middle East

tel: +31-347-324989  
salesEurope@redlake.com

 [www.redlake.com](http://www.redlake.com)

#### Japan

tel: +81-3-5639-2770  
salesJapan@redlake.com

Copyright © 2005  
Redlake, MASD, LLC  
All Rights Reserved  
HS-4 09/05

